



RUBBER HOUSEHOLD GLOVES
DG-HS-Y and DG-HS-B



DG-HS-Y

DG-HS-B

Description

Dromex® DG-HS series of re-useable flocked lined, soft touch household gloves are designed to protect the users' hands from the hazards of water and dirt whilst keeping them dry and breathable.

Available in yellow and blue, with diamond pattern palm provides grip especially when used in wet conditions. Diamond pattern wrist cuff and flock lining assists with ease of removal on gloves. The 10cm flute cuff also allows the glove to breathe and provides a good seal over chemical protective suits or on hands.

Suitable for use when working in laboratories, cleaning, janitorial and household applications where protection of the hand is required against dust and dirt.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Performs equivalent to the requirements of CE type examinations EN 420 for innocuousness.

Specifications

Style: Flock lined, reusable, waterproof latex gloves with wing thumb and diamond pattern palm and wrist.
 Liner: Cotton flock lined latex.
 Palm: Cotton flock lined latex 0.4mm ± 5 %
 Back: Cotton flock lined latex 0.31 mm ± 5 % impact protection.
 Cuff: 0.4mm, 10 cm Rolled cuff with diamond pattern for easier removal of glove.
 Mass: Part number DG-HS-Y ± 57 g per pair (XL); Part number DG-HS-B ± L56 g per pair (size L).

Packaging, Storage & Obsolescence


Packed in individual polybags and sold as 120 pairs per carton for shipping. Store away from humidity, in a cool, dry, dark place. Stored correctly, the gloves physical properties will not change for up to 18 months.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the gloves. Should this not be possible, it is advisable to ease left and right hand gloves off, using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below.



In order to maximise the gloves life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Sizes Available


Code	Size	Palm Length
DG-HS-Y-S	S	90mm (±2mm)
DG-HS-Y-M	M	100mm (±2mm)
DG-HS-Y-L	L	110mm (±2mm)
DG-HS-Y-XL	XL	115mm (±2mm)

Code	Size	Palm Length
DG-HS-B-S	S	90mm (±2mm)
DG-HS-B-M	M	100mm (±2mm)
DG-HS-B-L	L	110mm (±2mm)
DG-HS-B-XL	XL	115mm (±2mm)

** As per the EN420 standard, actual measurement of gloves are determined by the manufacturer, taking into account the behaviour of the glove material, its thickness (such as leather gloves, PVC gloves etc), elasticity and the intended use.*

** Sizing charts only serve as a guide. Sizes and measurements are for reference only. In order to make an informed decision, always try on the gloves as each glove features a unique construction to accommodate a wearer's preferences.*

Measurement Guide



Materials



1. Wing thumb
2. Palm with diamond pattern
3. 10cm Rolled cuff

Dromex: Unit 1, 1 Blase Road, New Germany, 3620, South Africa
 T. +27(31) 713 1960 E. info@dromex.co.za
 www.dromex.co.za